
ROOM STATUS MONITOR For Sensing Low Pressure Using High Accuracy



SERIES RSM Room Status Monitor is designed for critical low differential pressure applications that require stringent pressure monitoring and alarming. The Series RSM can be configured to monitor positive or negative pressure in protected environments and hospital isolation rooms per CDC guidelines. The RSM is a complete system with a graphic user interface which enables access to pressure, security, calibration, and alarm setup. The RSM has a NEMA 1 (IP20) rated fire retardant plastic for indoor applications.

a a

FEATURES/BENEFITS

- Accurately monitor protective environments for negative or positive pressure ensuring safety and reducing risk of catastrophic events
- Audible and visual alarm provides immediate local alerts allowing corrective action to be taken quicker to eliminate the problem from becoming widespread
- · Password protected set up menu helps to insure no errors by untrained personnel
- Optional BACnet communication from devices provides integration into building control system for automated control and centralized monitoring and alarming

APPLICATIONS

•	Hospital	isolation	wards
---	----------	-----------	-------

Clean rooms

Pharmaceutical
Manufacturing
Animal facilities

MODEL CHART						
Model*	Operating Range	Model**	Operating Range			
RSM-1-A	±0.05 in w.c.	RSM-1-B	±0.05 in w.c.			
RSM-2-A	±0.1 in w.c.	RSM-2-B	±0.1 in w.c.			
RSM-3-A	±0.25 in w.c.	RSM-3-B	±0.25 in w.c.			
RSM-4-A	±0.5 in w.c.	RSM-4-B	±0.5 in w.c.			
RSM-5-A	±1 in w.c.	RSM-5-B	±1 in w.c.			
RSM-6-A	±2.5 in w.c.	RSM-6-B	±2.5 in w.c.			
*Excitation/Output: 24 VAC/4 to 20 mA or 0 to 5 or 0 to 10 VDC.						
**Excitation/Output: 120 VAC/4 to 20 mA or 0 to 5 or 0 to 10 VDC.						
Note: For optional BACnet communication change end from -A						
to -C for 24 VAC power or from -B to -D for 120 VAC power models						

SPECIFICATIONS

Service: Air or non-conductive, nonexplosive gases.Switch Type: SPST.Accuracy: ±0.5% FS.Temperature Limits: 32 to 120°F (0 to 50°C).Loop Resistance (4 to 20 mA output): 0 to 510 Ω.Humidity Limits: 5 to 95% relative humidity (non-condensing).Electrical Connections: Barbed fittings for 3/16° ID tubing.Altitude: 6561 ft (2000 meters) max.Process Connections: Barbed fittings for 3/16° ID tubing.Thermal Effects: ±0.03% FS/°F.Process Connections: Barbed fittings for 3/16° ID tubing.Yeresure Limits: ±15 in w.c. (±3.7 kPa).Supply Voltage: Order code A (24 VAC):Supply Voltage: Order code A (24 VAC):gang metal electrical box using 4x4″ plaster ring adapter.18 to 32 VAC, 50 to 60 Hz; Order code Hz; Main supply voltage fluctuations up to 10%.Dimensions: 8' H x 5.4" W x 1.8" DPower Requirements: 5 W.Communications: BACnet MSTPPower Consumption (Voltage output): 5 W.Agency Approvals: CE, CSA (RSM only).5 W.Output Signal: Selectable 4 to 20 mACavirre).0 to 5 VDC (3-wire), or 0 to 10		
	plosive gases. Accuracy: ±0.5% FS. Temperature Limits: 32 to 120°F (0 to 50°C). Humidity Limits: 5 to 95% relative humidity (non-condensing). Altitude: 6561 ft (2000 meters) max. Thermal Effects: ±0.03% FS/°F (± 0.05% FS/°C). Pressure Limits: ±15 in w.c. (±3.7 kPa). Supply Voltage: Order code A (24 VAC): 18 to 32 VAC, 50 to 60 Hz; Order code B (120 VAC): 85 to 265 VAC, 50 to 60 Hz; Main supply voltage fluctuations up to 10%. Power Requirements: 5 W. Power Consumption (Voltage output): 5 W. Output Signal: Selectable 4 to 20 mA (2-wire), 0 to 5 VDC (3-wire), or 0 to 10	Loop Resistance (4 to 20 mA output): 0 to 510 Ω. Electrical Connection: Removable terminal block. Process Connections: Barbed fittings for 3/16" ID tubing. Enclosure Rating: NEMA 1 (IP20) rated for indoor applications. Housing: Fire retardant plastic. Mounting: Mount to standard double gang metal electrical box using 4x4" plaster ring adapter. Dimensions: 8" H x 5.4" W x 1.8" D (20.3 H x 13.7 W x 4.1 D cm). Weight: 1.5 lb (680 g). Communications: BACnet MSTP ASC optional. Agency Approvals: CE, CSA (RSM

ACCESSORY

Model Excitation/Output

A-285 Remote alarm annunciator with visible/audible alarm and acknowledge switch

Process Tubing Options: See page 443 (Gage Tubing Accessories)